

TENGA Spinner Tetra

Product Specifications

Size (D x W x H mm): 56 x 56 x 140

Insertion Length (mm): Stretches to approx. 170*

Insertion Width (mm): Stretches to approx. 55*

**Product stretches to accommodate almost any size.*

Weight (g): 204

Materials:

Casing: PP, PS, PE

Product: Elastomer

With proper washing and care, the TENGA SPINNER is reusable. Please note that product longevity may vary in accordance with methods and strength of use, lubricant choice, cleaning and storage methods, and overall maintenance.

Washing instructions:

- 1) Invert the insertion point of the SPINNER (up to the coil) and wash under running cold or tepid water.
- 2) Dry off with a towel.
- 3) Place the SPINNER on to its Drying Case to air dry.
- 4) Once completely dry, place into the case for storage.

<Warning>

- Wash with cold or tepid water.
- Use only neutral or mild soap. Soaps high in acid or alkaline content may damage product material.
- Do NOT wash with alcohol or other cleaners.
- Please ensure the product is completely clean and dry before storing to help avoid mold and other build-up.
- Lubricate both the inside and around the insertion point to allow for smooth entry. Insufficient lubrication may make it difficult to insert, or cause discomfort during use.